

The Siemens logo is displayed in a bold, teal, sans-serif font. It is positioned in the upper left corner of the page, set against a white rectangular background. The background of the entire page is a photograph of an industrial factory floor with robotic arms and car chassis.

SIEMENS

Ingenuity for life

The main title is presented in a large, white, sans-serif font. It is centered within a teal rectangular box that overlaps the bottom right portion of the factory background image. The text is clear and legible against the dark teal background.

Siemens 3VA Circuit Breakers

Sales Brief

usa.siemens.com/3VA

	Amps	AIC at 480V	Poles				Thermal Mag	Electronic Trip
			1	2	3	4		
125A frame	15 -125	up to 65kA	X	X	X	X	X	
150A frame	40-150A	up to 100kA		X	X	X		X
250A frame	100-250A	up to 150kA		X	X	X	X	X
400A frame	250-400A	up to 150kA		X	X	X	X	X
600A frame	400-600A	up to 150kA		X	X	X	X	X

Siemens 3VA Circuit Breakers

Sales message:

Siemens 3VA family of UL489 Circuit Breakers cover the range of circuit protection applications including 1-pole to 4-pole applications ranging from 15 amps to 600 amps. This product is intended to enhance our existing offering and is not replacing either or VL or Sentron line. It is available in a variety of fixed mount thermal-magnetic (TM) and electronic (ETU).

Business drivers:

To meet ever-changing market needs, 3VA breakers are flexible, modular in design, enabling intuitive field adjustments. The 3VA family of circuit breakers accommodates and provides system-wide innovation, economical solutions with a variety of internal and external accessory options to exceed the ever changing demands of customer requirements.

Competition:

- ABB - Tmax
- Schneider (SqD) - PowerPact
- Eaton (Cutler-Hammer) – Series G
- GE – Spectra and Record Plus
- Allen-Bradley – 140G (Brand Labeled ABB)

Five reasons to buy:

- Compact Design as compared to the existing Siemens legacy products as well as our competitors
- Highly configurable with numerous internal and external accessories from lugs, to motor operators and plug in/Draw Out Units and everything in between. Not to mention all internal accessories are universal to the product line.
- Metering is an option in our 8 Series ETU breaker with various communication protocols- ProfiBus, Modbus and ProfiNet. Additionally can be integrated into TIA portal!
- Revised pricing structure, lower list and into stock prices as well as equal as or better than current net pricing levels!
- Tools, tools, tools! Configurator for easy selection as well as easily accessible 2D/3D drawings and cut sheets



3VA5- Thermal Magnetic TU™

- 15A through 600A
- 125A frame rated 65kA @ 480V AC
- 25A, 4000A, 600A frames rated 100kA @ 480V AC
- Compact design
- Removable accessory cover for internal accessories



3VA6- Electronic TU (ETU)

- Frame sizes of 150, 250, 400 and 600 amps
- Interrupting ratings up to 150kA @ 480V AC
- Electronic trip units in 3 variants (Series 3, 5 and 8)
- 8 Series - Metering Capable
- Communications of ProfiNet, ProfiBus or Modbus RTU available



Options

- Wide range of lug combinations
- Illuminated rotary operator
- MaxFlex and variable depth flange operators
- Extensive offering of system internal switches; shunt trips, aux contacts, late-break contacts, alarm contacts and more that fit the entire family

**Published by
Siemens 2019**

Siemens Industry, Inc.
5400 Triangle Parkway
Norcross, GA 30092

Siemens Technical Support: 1-800-333-7421
info.us@siemens.com

Printed in USA-CP
Order No. CPBR-3VASS-0319
All Rights Reserved
© 2019, Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.

