

1 IF IN DOUBT ASK  
DO NOT SCALE


**EU EXPORT CONTROLS**

**ECCN: N**

**AL: N**

This document is not Export Controlled unless sending to Critical Countries.

Sr. no.	Parts
1	Transparent cover with gasket inside
2	Relay Mounting Screw Kit



NOTE:  
THE  $\phi 4.5$  HOLES TO BE CLEARANCE AND RELAYS MOUNTED USING  
M4x20 ROUND SS STUDS (4 nos.), M4 KNURLED SCREWS (4 nos.),  
LOCK WASHERS(4 nos.) and NUT (4 nos.)

**MATERIAL:**

Dimensions in millimetres : Surface texture in micrometres.

Machine where marked ✓

For explanation of dimensions, tolerances, notes etc. see B.S.308.

Limit on untoleranced unmachined-dimensions  $\pm$  \_\_\_\_\_

Limits on untoleranced machined-dimensions, to B.S.4500;

ie. up to 6 $\pm$ 0.1; over 30 to 120 $\pm$ 0.3; over 315 $\pm$ 0.8;

over 6 to 30 $\pm$ 0.2; over 120 to 315 $\pm$ 0.5;

General unmachined angular tolerance  $\pm$  \_\_\_\_\_

Finish:

Treatment:

Title:

7SR45 V3 WITH TRANSPARENT COVER ASSEMBLY

Copyright ©

Siemens Protection Devices Ltd. Hebburn

First used on:

Similar Articles:

Supersedes:

Original Scale.

: NTS

Drwg. No.

2995X10026

ISSUE	DATE	CHANGE NOTED
1A	01/11/19	

**NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED**

DRAWN	AMAR	CHECKED	VENKATESH	APPROVED	MANI	DATE	01/11/19	IE	OPS	PCP	Purch. Spec.	TQ	EAC	CE	STD	A3
-------	------	---------	-----------	----------	------	------	----------	----	-----	-----	--------------	----	-----	----	-----	----