



**NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED**



FOR FULL APPLICATION DIAGRAM
SEE 2659W50007 AND 2659W50008.

- ○ make contact
- ⊠ break contact
- ⊞ ○ c/o contact
- ⊖ metering point
- ⌋ plug bridge - shorting
- ② ext. conn
- unused conn
- ⌋ 15Kv barrier
- ⊞ test socket - shorting
- ⊖ plug & socket

OUTER TERMINAL BLOCK ASSY 'A' :-
 ASSEMBLY INSTRUCTIONS:-
 TYPICAL ASSEMBLY DRAWING 2995G10029.
 AT INDICATED POSITIONS FIT AS FOLLOWS:
 S - FIT STANDARD CONTACT 2995B10051
 HC - FIT 'HEAVY CURRENT' KIT 2995G10030
 WHERE ⊖ ○ IS SHOWN FIT CT SHORTING
 KIT 2995G10031
 POSITIONS SHOWN BLANK ARE UNUSED.
 ALL POSITIONS FIT SCREW 2106F12506.



			Title: INTERNAL WIRING DIAGRAM FOR 15KV PILOT SUPERVISION SEND END RELAY IN E12 CASE.		First used on:	
					Similar Articles:	
SIEMENS PROTECTION DEVICES LTD.			Original Scale.		Supersedes: Provisional issue 'A' dated 15/01/2013	
					Drg.No. 2659W50004	
1	10/03/13					
ISSUE	DATE	MOD.No.				
DRAWN: J. BURNETT			CHECKED: RD. WATSON		APPROVED: RD. WATSON	
			DATE: 01/03/2013		IE: OPS:	