



SIEMENS
Ingenuity for life

SIPROTEC 5

Applications

Unrestricted © Siemens AG 2017

[siemens.com/siprotec5](https://www.siemens.com/siprotec5)

SIPROTEC 5 Contents

SIEMENS
Ingenuity for life



[SIPROTEC 5 System](#)

[System engineering](#)

[Protection](#)

[Communication](#)

[Control](#)

[Power Quality](#)

[Digital Substation](#)

SIPROTEC 5 System

<u>SIP5-APN-001</u>	Properties and Functional Structure
<u>SIP5-APN-010</u>	DIGSI 5 Quick start for smart Engineering
<u>SIP5-APN-015</u>	Device and Power System Configuration
<u>SIP5-APN-022</u>	Time synchronization settings in SIPROTEC 5
<u>SIP5-APN-011</u>	Powerful commissioning with SIPROTEC 5
<u>SIP5-APN-028</u>	Time synchronization via IEEE 1588

SIPROTEC 5 System

<u>SIP5-APN-040</u>	Extension of BI/BO for busbar protection SIPROTEC 7SS85
<u>APN-041</u>	Arc Flash Protection for Medium Voltage Switchgears
<u>APN-042</u>	Protection and control devices for Medium Voltage Switchgears
<u>APN-047</u>	Line differential protection and TPZ class CT at one terminal

System engineering

<u>SIP5-APN-002</u>	SIPROTEC 5 application for Breaker-and-a-half solutions
<u>SIP5-APN-004</u>	Voltage selection for synch check in breaker-and-a-half application
<u>SIP5-APN-012</u>	Control of Breaker-and-a-half diameters and double busbar configurations
<u>SIP5-APN-018</u>	Breaker-and-a-half configuration: Automatic reclosing and leader follower
<u>SIP5-APN-023</u>	Change of setting groups with CFCs in SIPROTEC 5
<u>SIP5-APN-024</u>	Innovative solution for SIPROTEC 5 panels
<u>SIP5-APN-027</u>	Change of switching authority with function keys



System engineering

<u>SIP5-APN-031</u>	Breaker Pole Discrepancy function
<u>SIP5-APN-035</u>	Display of the power factor $\cos \varphi$ on the display
<u>SIP5-APN-036</u>	Porting CFC charts from DIGSI 4 projects to DIGSI 5
<u>APN-049</u>	Process Bus - Circuit Breaker Position feedback via GOOSE



New

Protection

<u>SIP5-APN-003</u>	Tapped Line Application
<u>SIP5-APN-016</u>	Distance protection with tele-protection (pilot protection) on an OHL feeder
<u>SIP5-APN-017</u>	Stub protection
<u>SIP5-APN-025</u>	SIPROTEC 7UT8 – Autotransformer bank with 2 sets of CT inside the delta connection of the compensation side
<u>SIP5-APN-026</u>	Sync Check with Voltage selection and VTs with different ratio
<u>SIP5-APN-029</u>	Ground fault detection of 4 feeders with 7SJ82 or 7SJ85 with 4x I, 4x U

Protection

<u>SIP5-APN-030</u>	Circulating Current High Impedance Differential Protection Using Multifunctional Relay 7SJ8
<u>SIP5-APN-033</u>	SIPROTEC 7SK85 Motor protection for Asynchronous Motors with Krondorfer Starter
<u>APN-045</u>	SIPROTEC 7UT86 as impedance protection in power transformer
<u>APN-050</u>	SIPROTEC 5 Main Protection Functions – Limit Overview


New

Control

<u>SIP5-APN-034</u>	Voltage control of transformers in parallel operation using SIPROTEC 7UT8x and the master-follower method
<u>SIP5-APN-038</u>	Acquisition of transformer tap positions via an analog measurement transformer

Communication

<u>SIP5-APN-005</u>	Protection Data Interface Application
<u>SIP5-APN-006</u>	Multiple communication options with SIPROTEC 5
<u>SIP5-APN-009</u>	Communication Architecture Under Cyber Security Aspects
<u>SIP5-APN-013</u>	Teleprotection scheme with SIPROTEC 5 devices
<u>SIP5-APN-019</u>	Flexible Engineering – Modeling the System with the Options of IEC 61850
<u>SIP5-APN-020</u>	PIXIT - Generation for SIPROTEC 5
<u>SIP5-APN-032</u>	Reliable transmission of trip signal with GOOSE
<u>APN-044</u>	Line differential protection in MPLS based communication networks



Power Quality

[SIP5-APN-037](#)

Selection of PMU functionality in SIPROTEC 5



Digital Substations with SIPROTEC 5 are the answer to trends and challenges

