

SIEMENS

Ingenuity for life

SIPROTEC 7SK82

Motor Protection

www.siemens.com/siprotek

Description

The SIPROTEC 7SK82 motor protection has been designed particularly for a cost-optimized and compact utilization of small to medium-sized motors. With its flexibility and the powerful DIGSI 5 engineering tool, SIPROTEC 7SK82 offers future-oriented system solutions with high investment security and low operating costs.

Main function	Motor protection for small to medium-sized motors (100 kW to 2 MW)
Inputs and outputs	4 current transformers, 4 voltage transformers (optional), 11 or 23 binary inputs, 9 or 16 binary outputs
Hardware flexibility	Different hardware quantity structures for binary inputs and outputs are available in the 1/3 base module. Adding 1/6 expansion modules is not possible; available with large or small display
Housing width	1/3 × 19"

Benefits

- Compact and low-cost motor protection
- Safety due to powerful protection functions
- Data security and transparency over the entire lifecycle of the plant save time and money
- Purposeful and simple operation of the devices and software thanks to user-friendly design
- Increased reliability and quality of the engineering process
- Consistent implementation of high safety and security mechanisms



SIPROTEC 7SK82

- Powerful communication components ensure safe and effective solutions
- Full compatibility between IEC 61850 Editions 1 and 2
- High investment security and low operating costs due to future-oriented system solution

Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Motor protection functions: Startup time monitoring, thermal overload protection for stator and rotor, re-start inhibit, unbalanced-load protection, load-jam protection
- Stator and bearing temperature monitoring via temperature sensors with external RTD unit
- Sensitive ground-fault protection (non-directional, directional) to detect stator ground faults
- Directional and non-directional overcurrent protection (shortcircuit protection) with additional functions

Safe and efficient

- Detection of ground faults in isolated or arc-suppression-coilground power systems
- Overvoltage and undervoltage protection
- Arc protection
- Power protection, configurable as active or reactive powerprotection
- Detection of current and voltage signals up to the 50th harmonic with high accuracy for selected protection functions (such as thermal overload protection) and operational measured values
- Control, synchrocheck and switchgear interlocking protection
- Graphical logic editor to create powerful automation functions in the device
- Single line representation in small or large display
- Integrated electrical Ethernet RJ45 for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- Two optional pluggable communication modules, usable for different and redundant protocols (IEC 61850, IEC 60870-5-103, IEC 60870-5-104, DNP3 (serial and TCP), Modbus TCP, PROFINET IO)
- Redundancy protocols PRP and HSR
- Cyber security in accordance with NERC CIP and BDWE Whitepaper requirements
- Secure serial protection data communication, also over great distances and all available physical media (fiber-optic cable, 2-wire connections and communication networks)
- Capturing operational measured variables and protection function measured values to evaluate the plant state, to support commissioning, and to analyze faults
- Phasor measurement unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Powerful fault recording (buffer for a max. record time of 80 s at 8 kHz or 320 s at 2 kHz)
- Auxiliary functions for easy tests and commissioning

Applications

- Protection against thermal overload of the stator from overcurrent, cooling problems or pollution
- Protection against thermal overload of the rotor during startup due to frequent startups, excessively long startups or blocked rotor
- Monitoring for voltage unbalance or phase outage
- Monitoring the thermal state and the bearing temperatures with temperature measurement
- Detection of idling drives of pumps and compressors, for example
- Detection of ground faults in the motor
- Protection against motor short circuits
- Protection against instability due to undervoltage



Siemens AG 2016
Energy Management Division
Freyeslebenstraße 1
91058 Erlangen, Germany

SIPROTEC 7SK82 Profile.docx
Printed in Germany | © 09.16 Siemens AG

E-Mail: support.energy@siemens.com
Tel: +49 180 524 70 00

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org) and cryptographic software written by Eric Young (eay@cryptsoft.com).