

SIEMENS

Ingenuity for life

SIPROTEC 7UT85

Transformer Differential Protection

www.siemens.com/siprotec

Description

The SIPROTEC 7UT85 transformer differential protection device has been designed specifically for the protection of two-winding transformers (2 sides). It is the main protection for the transformer and contains many other protection and monitoring functions. The additional protection functions can also be used as backup protection for protected downstream objects (such as cables or lines). In this regard you are also supported by the modular expandability of the hardware. With its modular structure, flexibility and the powerful DIGSI 5 engineering tool, SIPROTEC 7UT85 offers future-oriented system solutions with high investment security and low operating costs.

Main function	1 differential protection function (standard or auto transformer) with additional stabilization; up to 2 restricted ground-fault protection functions
Usable measuring points	5 x 3-phase current measuring points, 3 x 1-phase current measuring points, 3 x 3-phase voltage measuring points; expandable to 3 sides
Inputs and outputs	2 predefined standard variants with 8 current transformers, 7 to 19 binary inputs, 7 to 23 binary outputs
Hardware flexibility	Flexibly adjustable and expandable I/O quantity structure within the scope of the SIPROTEC 5 modular system
Housing width	1/3 x 19 inch to 2/1 x 19 inch

Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Transformer differential protection for two-winding transformers with versatile, additional protection functions; expandable to 3 windings



SIPROTEC 7UT85

- Transformer differential protection for phase-angle regulating transformers of the single core type and special transformers
- Applicable from average up to extra-high voltage
- Protection of standard power transformers, auto transformers and motors
- Typical properties of a transformer differential protection such as flexible adaptation to the transformer vector group, control of inrush and overexcitation processes, safe behavior in the case of current-transformer saturation with different degrees of saturation
- Adaptive adaptation of the operate curve to the transformer tap position
- Increased sensitivity with near-neutral-point ground faults through a separate restricted ground-fault protection
- Additional current and voltage inputs can be supplements for standard protection functions, such as overcurrent, voltage frequency and others

Modular and flexible

- Arc protection
- Voltage controller function ANSI 90V for two-winding transformers, three-winding transformers and grid coupling transformers with parallel control (master/follower, circuit reactive current minimization)
- Graphical logic editor to create powerful automation functions in the device
- Up to 4 pluggable communication modules, usable for different and redundant protocols (IEC 61850, IEC 60870-5-103, IEC 60870-5-104, DNP3 serial and TCP, Modbus TCP, PROFINET IO)
- Redundancy protocols PRP and HSR
- Cyber security to NERC CIP and BDWE Whitepaper requirements
- Secure serial protection data communication, even over great distances and all available physical media (optical fiber cable, 2-wire connections and communication networks)
- Capturing operational measured variables and protection function measured values to evaluate the plant state, to support commissioning, and to analyze faults
- Phasor measurement unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Powerful fault recording (buffer for a max. record time of 80 sec. at 8 kHz or 320 sec. at 2 kHz)
- Auxiliary functions for simple tests and commissioning
- Flexibly adjustable I/O quantity structure within the scope of the SIPROTEC 5 modular system

Benefits

- Safety due to powerful protection functions
- Data security and transparency over the entire lifecycle of the plant save time and money
- Purposeful and simple operation of the devices and software thanks to user-friendly design
- Increased reliability and quality of the engineering process
- High safety due to a consistent implementation of safety and security
- Powerful communication components ensure safe and effective solutions
- Full compatibility between IEC 61850 Editions 1 and 2
- Highly available Ethernet communication due to integrated Ethernet redundancy protocols PRP and HSR



Siemens AG

Energy Management Division
Freyeslebenstraße 1
91058 Erlangen, Germany

SIPROTEC 7UT85 Profile E7.5.docx
Printed in Germany | © 09.17 Siemens AG

E-Mail: support.energy@siemens.com
Tel: +49 180 524 70 00

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org) and cryptographic software written by Eric Young (eay@cryptsoft.com).