

Test Report

Report No.: 15-032-MS

Copy No.: 0

Contents: 92 Sheets

Test object: Three-pole vacuum circuit-recloser with control cubicle
Designation: 3AD3533-3 with vacuum interrupters VSR38-0-16 and controller 7SC8024
Rated voltage: 38 kV Rated normal current: 800 A Rated frequency: 50/60 Hz
Rated short-circuit breaking current: 16 kA
Manufacturer: Siemens AG, EM MS O SD BLN MF, Berlin
Client: Siemens AG, EM MS R&D OC, Berlin
Testing station: Prüffeld der Schaltwerke, Berlin
Date of test: February 17 -19, 2015
Applied test specifications:
IEC 62271-111, Edition 2.0, 2012-09

Tests performed:

Short-circuit tests for a rated current of 16 kA at a rated voltage of 38 kV and a rated frequency of 50 Hz in test-duty:

T100 :

14.4 kA up to 16.4 kA at 36.4 kV up to 41.3 kV and up to 45% dc-component for breaking tests
42.8 kA up to 45.7 kA at 39.7 kV up to 40.3 kV for making tests

Test results:

The test object has passed the above indicated tests without any objection. The proved performance and the results obtained comply with the requirements mentioned above.



M. Eiselt

M. Eiselt
Head of Testing Department
Medium Voltage Division

T. Rädisch

T. Rädisch
Head of High-Power/ High Voltage Testing Department
Medium Voltage Division

Berlin, July 15, 2015

The test results relate only to the items tested.

The authenticity of this document is guaranteed by the integrity of the seal label and seal ribbon. Without a written permission of Prüffeld der Schaltwerke it is not allowed to make reproduction in extracts of this document. Copying the cover sheet accompanied by sheet 2 and the sheets mentioned here is an exception.

Documents and Addresses

Accreditation

The Prüffeld der Schaltwerke, Berlin has been approved by the DAkkS (German accreditation body) according to EN ISO/IEC 17025 for tests in the field of high-voltage switchgear and controlgear and power engineering equipment (Registration-No. D-PL-11055-10-01).

Under reference to EN ISO/IEC 17025 the Prüffeld der Schaltwerke states the following:

- The accreditation of the Prüffeld der Schaltwerke or any of its test reports by themselves in no way constitute or imply product approval by DAkkS or any other body.
- If someone refers to a test in an accredited Prüffeld der Schaltwerke this reference shall include the accreditation body, i.e. DAkkS, the relevant scope of the accreditation and the appropriate registration number.

PSW-Documents

A Certificate

is issued for type tests which have successfully been carried out in full compliance with the relevant specifications or standards valid at the time of the test. For these tests the equipment under test must be clearly identified by technical description, drawings and additional specifications.

A Test Document

is issued for parts of type tests which have successfully been carried out in full compliance with the relevant specifications or standards valid at the time of test. For these tests the equipment under test must be clearly identified by technical description, drawings and additional specifications.

A Test Report

is issued for all other tests which have been carried out according to specifications, standards and/or clients instructions. Similarly, this test report contains all test results, details of the conditions under which the tests were carried out, also details relating to the behaviour of the equipment during test, and its condition after the tests.

A Test Confirmation

is issued immediately after the tests. It confirms that the tests have been conducted and is valid only until publishing the detailed results in an entire document.

Addresses

Testing Station: Prüffeld der Schaltwerke, Berlin
Siemens AG
EM MS R&D OC TD
Nonnendammallee 104
13629 Berlin
Germany

Manufacturer: Siemens AG
EM MS O SD BLN MF
Nonnendammallee 104
13629 Berlin
Germany

Client: Siemens AG
EM MS R&D OC
Nonnendammallee 104
13629 Berlin
Germany

Technical Data of Test Object Circuit Recloser

Test object: Three-pole automatic vacuum circuit recloser including control cubicle
Designation: 3AD3533-3 with vacuum interrupters VSR38-0-16 and controller 7SC8024
Manufacturer: Siemens AG, EM MS O SD BLN MF, Berlin
Serial No.: S 3AD/00004194
Year of manufacture: 2015
Drawing No.: Drawings and parts lists - see sheet 6

Ratings assigned by the manufacturer:

Rated voltage	38 kV	
Rated normal current	800 A	
Rated frequency	50/60 Hz	
Rated lightning impulse withstand voltage	170 kV	
Rated power-frequency withstand voltage	70 kV	
Rated peak withstand current	42 kA	
Rated short-time withstand current	16 kA	
Rated duration of short-circuit	3 s	
Rated symmetrical making current (rms)	16 kA	
Peak factor [i_p/I]	2.6	
Rated symmetrical interrupting current (rms)	16 kA	
DC component of the rated short-circuit breaking current (Valid for a minimum clearing time of 50 ms and a time constant of 45 ms)	33 %	
Rated transient recovery voltage	71.7 kV	
Rate of rise of transient recovery voltage	1.29 kV/ μ s	
First-pole-to-clear factor	1.5	
Rated operating sequence	O - 0.2 s - CO - 3 s - CO - 3 s - CO	
Arc extinguishing medium	Vacuum	
Insulating medium	Epoxy / Air / Silicone	
Driving mechanism (type)	Magnetic drive	
Number of poles	3	
Number of units per pole	1	
Rated opening time	< 35 ms	
Rated minimum tripping current	40 A	
Rated control voltage	110-230 V	a.c.
Rated frequency of control voltage	50/60 Hz	
Rated line-charging breaking current	5 A	
Rated cable-charging breaking current	40 A	
Rated single capacitor bank breaking current	400 A	

Further data:

Serial number of vacuum interrupter in pole L1 / L2 / L3	160 / 190 / 192
Pole centre distance	375 mm

Essential characteristics:

Serial number of control cubicle:	belongs to Recloser switch unit S 3AD/00004194
Controller type:	7SC8024-3BB97-3FB5/CC
Serial number of controller:	BF1503508319
Software Version	V04.20.04