



SIEMENS
Ingenuity for life



Applications

SIPROTEC 5

SIPROTEC 5 Applications

Table of Contents



- SIPROTEC 5 System
- System engineering
- Protection
- Communication
- Control
- IoT Connectivity

SIPROTEC 5 System

SIP5-APN-001	Properties and Functional Structure
SIP5-APN-010	DIGSI 5 Quick start for smart Engineering
SIP5-APN-015	Device and Power System Configuration
SIP5-APN-022	Time synchronization settings in SIPROTEC 5
SIP5-APN-011	Powerful commissioning with SIPROTEC 5
SIP5-APN-028	Time synchronization via IEEE 1588
APN-064	Time Synchronization of Phasor Measurement Unit (PMU) with PTP – IEEE1588
SIP5-APN-037	Selection of PMU functionality in SIPROTEC 5

New with
V7.90

SIPROTEC 5 System

<u>SIP5-APN-040</u>	Extension of BI/BO for busbar protection SIPROTEC 7SS85
<u>APN-041</u>	Arc Flash Protection for Medium Voltage Switchgears
<u>APN-042</u>	Protection and control devices for Medium Voltage Switchgears
<u>APN-047</u>	Line differential protection and TPZ class CT at one terminal

System engineering

<u>SIP5-APN-002</u>	SIPROTEC 5 application for Breaker-and-a-half solutions
<u>SIP5-APN-004</u>	Voltage selection for synch check in breaker-and-a-half application
<u>SIP5-APN-012</u>	Control of Breaker-and-a-half diameters and double busbar configurations
<u>SIP5-APN-018</u>	Breaker-and-a-half configuration: Automatic reclosing and leader follower
<u>SIP5-APN-023</u>	Change of setting groups with CFCs in SIPROTEC 5
<u>SIP5-APN-024</u>	Innovative solution for SIPROTEC 5 panels
<u>SIP5-APN-027</u>	Change of switching authority with function keys

System engineering

<u>SIP5-APN-031</u>	Breaker Pole Discrepancy function
<u>SIP5-APN-036</u>	Porting CFC charts from DIGSI 4 projects to DIGSI 5
<u>APN-049</u>	Process Bus - Circuit Breaker Position feedback via GOOSE
<u>APN-054</u>	Trip counter with Pulse Metered Value

Protection

<u>SIP5-APN-003</u>	Tapped Line Application
<u>SIP5-APN-016</u>	Distance protection with tele-protection (pilot protection) on an OHL feeder
<u>SIP5-APN-017</u>	Stub protection
<u>SIP5-APN-025</u>	SIPROTEC 7UT8 – Autotransformer bank with 2 sets of CT inside the delta connection of the compensation side
<u>SIP5-APN-026</u>	Sync Check with Voltage selection and VTs with different ratio
<u>SIP5-APN-029</u>	Ground fault detection of 4 feeders with 7SJ82 or 7SJ85 with 4x I, 4x U

Protection

<u>SIP5-APN-030</u>	Circulating Current High Impedance Differential Protection Using Multifunctional Relay 7SJ8
<u>SIP5-APN-033</u>	SIPROTEC 7SK85 Motor protection for Asynchronous Motors with Krondorfer Starter
<u>APN-045</u>	SIPROTEC 7UT86 as impedance protection in power transformer
<u>APN-050</u>	SIPROTEC 5 Main Protection Functions – Limit Overview
<u>APN-052</u>	Directional ground-fault protection
<u>APN-053</u>	Auxiliary devices for generator protection



Protection

<u>APN-055</u>	Distance protection ground fault direction stabilized with 67Ns for high impedance resistive ground
<u>APN-056</u>	Application for low voltage with 400 V measurement without voltage transformer
<u>APN-059</u>	2nd Harmonic Blocking 3I0 Protection
<u>APN-060</u>	Low Impedance restricted ground fault 87N
<u>APN-061</u>	Impedance Protection 3-winding Transformer
<u>APN-063</u>	End Fault Protection

Protection

APN-065	Line Differential protection [87L] for 2-phase systems with nominal frequency of 50Hz or 60Hz
APN-069	Scott Transformer Application with Differential Protection SIPROTEC 7UT8



Control

<u>SIP5-APN-034</u>	Voltage control of transformers in parallel operation using SIPROTEC 7UT8x and the master-follower method
<u>SIP5-APN-038</u>	Acquisition of transformer tap positions via an analog measurement transformer

Communication

<u>SIP5-APN-005</u>	Protection Data Interface Application
<u>SIP5-APN-006</u>	Multiple communication options with SIPROTEC 5
<u>SIP5-APN-009</u>	Communication Architecture Under Cyber Security Aspects
<u>SIP5-APN-013</u>	Teleprotection scheme with SIPROTEC 5 devices
<u>SIP5-APN-019</u>	Flexible Engineering – Modeling the System with the Options of IEC 61850
<u>SIP5-APN-020</u>	PIXIT - Generation for SIPROTEC 5
<u>SIP5-APN-032</u>	Reliable transmission of trip signal with GOOSE
<u>APN-044</u>	Line differential protection in MPLS based communication networks

IoT Connectivity

<u>IoT-APN-001</u>	SIPROTEC 5 Engineering Guide for SIPROTEC 5
<u>IoT-APN-006</u>	SIPROTEC 5 Engineering Guide for SIPROTEC Dashboard
APN-058	Access via VPN to SIPROTEC DigitalTwin

Disclaimer



Subject to changes and errors. The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

All product designations, product names, etc. may contain trademarks or other rights of Siemens AG, its affiliated companies or third parties. Their unauthorized use may infringe the rights of the respective owner.